


Garant

Fleece compact disc, Ø 115 mm, Grit equivalent: 100



Order data

Order number	566991 100
GTIN	4045197721242
Item class	51M

Description

Version:

Crimped-in fibrous fleece with resin-bonded aluminium oxide grit permits **metal removal and finishing in a single operation.**

Application:

For surface and edge grinding on angle grinders (recommended speed 6000 rpm). **Hard** version with coarse grits, very stable edge.

maximum circumferential speed: 60 m/s

Bore Ø: 22.23 mm

Grit designation: coarse

Degree of hardness: hard

Bore Ø: 22.23 mm

Version: 8 A coarse

Technical description

Grit designation	coarse
recommended speed	6000 min ⁻¹
Degree of hardness	hard
Grit equivalent	100

Version	8 A coarse
Disc Ø	115 mm
Bore Ø	22.23 mm
Iron, sulphur and chlorine constituents	< 0.1 %
Shape description	flat
Product name attribute	Ø 115 mm
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	60 m/s
Type of product	Compact disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		