


**HOLEX****Abrasive sleeve, conical (A) 40 grit coarse, largest sleeve  $\varnothing$  x sleeve width:  
36X60mm****Order data**

Order number	553850 36X60
GTIN	4045197722959
Item class	52E

**Description****Version:**

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion.

**Aluminium Oxide (A)** for general-purpose grinding work.

**The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place.** The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

**Application:**

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

**Suitable for:**

Abrasive sleeve holder No. 553830.

**Technical description**

Sleeve width	60 mm
largest sleeve $\varnothing$	36 mm
Grit	40
Grit designation	coarse

Grinding media	Standard Aluminium Oxide
Grinding medium code	A
Sleeve shape	conical
Type of product	Abrasive sleeve

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
dry	suitable		

## Accessories

Abrasive sleeve holder slit, conical shank 6 mm Ø largest  
Øxhead length 36X60 mm

553830 36X60