

Garant GRIDLINE

Casing 16G with door hinged on the right, Height / number of drawers: 800**Order data**

Order number	927310 800
GTIN	4062406108373
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. **Aluminium handles** with labelling strips that can be exchanged and rewritten. Can be locked centrally with cylinder lock.

Door hinged on the right.

Fitted with:

Door height, mm: 700

Number of height-adjustable storage shelves: 1

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Sizes 600 and 700 suitable only for Ready-to-go workbenches.

Technical description

Usable height	700 mm
Width	400 mm

Height	800 mm
Number of doors	1
Weight	26.8 kg
Number of drawers	0
Door usable height	700 mm
Depth	650 mm
Door height	700 mm
Usable width	350 mm
Door stop	right-hand
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Workbench casing

Accessories

Slide handle for GridLine Type KO12	914226 KO12
Fixed shelf, galvanised Type 1	927515 1
Shelf carriers for shelves of workbenches Type 12	927094 12