

Garant GRIDLINE

Drawer, 12×20G, Drawer front height: 50mm**Order data**

| | |
|--------------|---------------|
| Order number | 927500 50 |
| GTIN | 4062406109776 |
| Item class | 9GG |

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with modular dividing material.

Suitable for:

All cabinet casings 16G.

Colour:

Drawer unit body RAL 7035 light grey, drawers RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|-------------------------------------|------------------|
| Usable height | 25 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Front height | 50 mm |
| Weight | 6.7 kg |
| Drawer usable area in G | 12×20 |
| Usable width in G | 12 |
| Usable depth in G | 20 |
| Application range | Workbench casing |
| Usable depth | 500 mm |

| | |
|--|---|
| Usable width | 300 mm |
| with individual drawer release system | no |
| Material thickness | 1 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 12×20G |
| Type of product | Drawer |