



Combination face mill adapter, SK 50 A = 55, Spigot Ø d1: 22mm



Order data

Order number	302515 22
GTIN	4062406111090
Item class	32A

Description

Version:

Internal thread for manual clamping.

Application:

With drive key for milling cutters **with longitudinal groove**, e.g. DIN 841.

With face mill drive ring for milling cutters with **transverse slots**, DIN 1880.

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Special toggle spanner No. 309840.

Technical description

Milling mandrel length L ₄	31 mm
Milling mandrel length L ₃ with drive ring	19 mm
Thread M	M24
Overall length L	201 mm
Spare drive ring No. 309870	22
Overhang dimension A	55 mm
Suitable toggle spanner No. 309840	22
Spare milling cutter lock screw No. 309860 / 309861	22

Clamping $\varnothing D_1$	22 mm
Adapter	SK 50 A = 55
Standard	DIN 6358
Arbor standard	DIN 2080
Concentricity	$\leq 6 \mu\text{m}$
Type of product	Milling cutter spigot