

**Abrasive sleeve, conical (ZA), 40 grit coarse, largest sleeve Ø× sleeve width: 20X63mm****Order data**

Order number	553871 20X63
GTIN	4045197723307
Item class	52E

**Description****Version:**

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion.

**Zirconium Aluminium Oxide (ZA).**

**The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place.** The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

**Application:**

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

**Suitable for:**

Abrasive sleeve holder No. 553830.

**Technical description**

Grit	40
Sleeve width	63 mm
largest sleeve Ø	20 mm
Grit designation	coarse
Grinding media	Zirconium aluminium oxide

Grinding medium code	ZA
Sleeve shape	conical
Type of product	Abrasive sleeve

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Wood	suitable only under restricted conditions		
dry	suitable		

## Accessories

Abrasive sleeve holder slit, conical shank 6 mm Ø largest  
Ø×head length 20X63 mm

553830 20X63