


Garant**Perforated panel double-sided, suitable for type: 1000****Order data**

Order number	928071 1000
GTIN	4062406112691
Item class	91P

Description**Version:**

Of sturdy sheet metal, inclined for clean organisation of tool storage.

Perforated panel in **double-sided version** can be **independently equipped** on both sides.

Perforated panels made of folded sheet metal □ 9×9 mm at 37 mm intervals for mounting perforated panel accessories.

Suitable for:

For bolting between the support columns No. 928010, in materials supply trolley No. 918590 and for divider walls No. 955430 and 955431.

Colour:

RAL 7035 light grey **powder coated**.

Note:

See group 95 for accessories for perforated back panels.

Technical description

Width	920 mm
Weight	12 kg
Perforated panel version	double-sided
Safe working load	100 kg
Height	481 mm
Depth	25 mm

suitable for type	1000 mm
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated rear panel

Accessories

Multimedia swivel arm with multi-function mounting Number of joints 1	928270 1
Support column for hooking into perforated panel Height 481 mm	928060 481
Multifix suitable for type 500	928201 500
Multimedia swivel arm with notebook holder Number of joints 2	928275 2
Multifix suitable for type 300	928201 300
Multimedia swivel arm with multi-function mounting Number of joints 2	928270 2