

**Garant**
**ER collet chuck mini / slim Form ADB, SK 50 A = 100, for ER collet size: 11**

**Order data**

Order number	300667 11
GTIN	4062406109455
Item class	31A

**Description**
**Version:**

Clamping nut finely balanced **for HSC**. ER11 through bored. Shanks hard turned (smooth cutting action).

**Supplied with:**

High speed ER mini nut No. 309650.

**Optional extras:**

ER collets No. 308881 – 309434, ER lock wrench No. 309740.

**Technical description**

Clamping range	0.5 - 7 mm
Suitable chuck key No. 309740	11
Overhang dimension A	100 mm
External $\varnothing$ D	16 mm
Usable length $L_N$	66 mm
Clamping $\varnothing$ $D_1$	1-7 mm
Adapter	SK 50 A = 100
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

## Accessories

ER collet Nominal clamping Ø d 4 mm	308918 4
Pull stud 90°sealed suitable for steep tapers 50	308790 50
ER collet Nominal clamping Ø d 6 mm	308918 6
Pull stud 60°sealed suitable for steep tapers 50	308785 50
ER collet Nominal clamping Ø d 2 mm	308881 2
Pull studForm B suitable for steep tapers 50	308640 50
ER collet Nominal clamping Ø d 2 mm	308918 2
ER collet Nominal clamping Ø d 3 mm	308881 3
Pull studsealed, form B suitable for steep tapers 50	308620 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studsealed suitable for steep tapers 50	308660 50
ER collet Nominal clamping Ø d 5 mm	308881 5
ER collet Nominal clamping Ø d 6 mm	308881 6
Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
ER collet Nominal clamping Ø d 1 mm	308881 1
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50

Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet Nominal clamping Ø d 7 mm	308881 7
ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
Pull studForm A suitable for steep tapers 50	308600 50
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet Nominal clamping Ø d 5 mm	308918 5
Torque wrenchwith reversible ratchet maximum torque 200 N-m	656050 200
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
ER collet Nominal clamping Ø d 1 mm	308918 1
ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 7 mm	308918 7
ER collet Nominal clamping Ø d 3 mm	308918 3
ER collet set 13 pieces 1–7 mm	309010
ER collet for machine taps Nominal clamping Ø d 3,5 mm	309399 3,5
ER collet for machine taps Nominal clamping Ø d 4 mm	309399 4
ER collet for machine taps Nominal clamping Ø d 4,5 mm	309399 4,5
ER colletwith seal Nominal clamping Ø d 4 mm	308882 4
ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet for machine taps Nominal clamping Ø d 6 mm	309399 6
ER collet for machine taps Nominal clamping Ø d 2,8 mm	309399 2,8
ER colletwith seal Nominal clamping Ø d 6 mm	308882 6
ER collet for machine taps Nominal clamping Ø d 2,5 mm	309399 2,5
ER collet set 7 pieces 1–7 mm	309155

ER colletwith seal Nominal clamping  $\varnothing$  d 3 mm

308882 3