



Combination face mill adapter, SK 50 A = 55, Spigot Ø d1: 32mm



Order data

Order number	302515 32
GTIN	4062406111113
Item class	32A

Description

Version:

Internal thread for manual clamping.

Application:

With drive key for milling cutters **with longitudinal groove**, e.g. DIN 841.

With face mill drive ring for milling cutters with **transverse slots**, DIN 1880.

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Special toggle spanner No. 309840.

Technical description

Thread M	M24
Overall length L	206 mm
Overhang dimension A	55 mm
Milling mandrel length L ₃ with drive ring	24 mm
Milling mandrel length L ₄	38 mm
Spare drive ring No. 309870	32
Suitable toggle spanner No. 309840	32
Spare milling cutter lock screw No. 309860 / 309861	32

Clamping $\varnothing D_1$	32 mm
Adapter	SK 50 A = 55
Standard	DIN 6358
Arbor standard	DIN 2080
Concentricity	$\leq 6 \mu\text{m}$
Type of product	Milling cutter spigot