


Garant**Perforated panel single-sided, suitable for type: 1500****Order data**

Order number	928070 1500
GTIN	4062406112677
Item class	91P

Description**NOTE: Colour selection possible****Version:**

Of sturdy sheet metal, inclined for clean organisation of tool storage. Perforated panel in double-sided version can be independently equipped on both sides.

Perforated panels made of sheet metal □ 9×9 mm at 37 mm intervals for mounting perforated panel accessories.

Suitable for :

For bolting between the support columns in roller cabinet No. 918590 and dividers.

Colour:

RAL 7035 light grey **powder coated**.

Note:

See group 95 for accessories for perforated back panels.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 481 mm

Width: 1420 mm

Depth: 25 mm

Safe working load: 100 kg

Weight: 9 kg

Technical description

Depth	25 mm
Width	1420 mm

Safe working load	100 kg
suitable for type	1500 mm
Height	481 mm
Perforated panel version	single-sided
Weight	9 kg
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated rear panel

Accessories

Multifix suitable for type 300	928201 300
Multifix suitable for type 1000	928201 1000
Multifix suitable for type 500	928201 500
Support column for hooking into perforated panel Height 481 mm	928060 481
Multimedia swivel arm with multi-function mounting Number of joints 1	928270 1
Multimedia swivel arm with multi-function mounting Number of joints 2	928270 2
Multimedia swivel arm with notebook holder Number of joints 2	928275 2