


## Garant

### Slim hydraulic chuck, HSK-A 100 A = 120, Clamping $\varnothing$ D1: 8mm



#### Order data

|              |               |
|--------------|---------------|
| Order number | 307543 8      |
| GTIN         | 4062406114978 |
| Item class   | 31A           |

#### Description

##### Version:

- **Extremely slim design (3°-contour).**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

##### Advantage:

- **Temperature-resistant due to completely enclosed system, i.e. no soldered pressure chambers.**
- **Ideal damping characteristics.**
- **High transmissible torques, providing high process reliability.**

##### Application:

Especially in operations in toolmaking and mould making.

**Wherever reduced interference contours are required.**

For drilling, reaming and milling.

For clamping tools with shank tolerance h6.

##### Supplied with:

Hexagon socket drive with T-handle.

##### Optional extras:

Reducing sleeves No. 302135 – 302165.

#### Technical description

|                                       |      |
|---------------------------------------|------|
| Clamping $\varnothing$ D <sub>1</sub> | 8 mm |
|---------------------------------------|------|

|                                       |                          |
|---------------------------------------|--------------------------|
| External $\varnothing$ D              | 50 mm                    |
| $\varnothing$ D <sub>3</sub>          | 21.45 mm                 |
| $\varnothing$ D <sub>2</sub>          | 14 mm                    |
| Overhang dimension A                  | 120 mm                   |
| L <sub>2</sub>                        | 71 mm                    |
| Adapter                               | HSK-A 100 A = 120        |
| Arbor standard                        | DIN 69893                |
| Arbor standard                        | ISO 12164-1              |
| Shape                                 | A                        |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm      |
| Concentricity                         | $\leq 3 \mu\text{m}$     |
| Machining strategy                    | HPC                      |
| Machining strategy                    | HSC                      |
| Type of product                       | Hydraulic clamping chuck |