


Garant**Perforated panel double-sided, suitable for type: 1500****Order data**

Order number	928071 1500
GTIN	4062406112707
Item class	91P

Description**Version:**

Of sturdy sheet metal, inclined for clean organisation of tool storage.

Perforated panel in **double-sided version** can be **independently equipped** on both sides.

Perforated panels made of folded sheet metal □ 9×9 mm at 37 mm intervals for mounting perforated panel accessories.

Suitable for:

For bolting between the support columns No. 928010, in materials supply trolley No. 918590 and for divider walls No. 955430 and 955431.

Colour:

RAL 7035 light grey **powder coated**.

Note:

See group 95 for accessories for perforated back panels.

Technical description

Weight	18 kg
suitable for type	1500 mm
Safe working load	100 kg
Perforated panel version	double-sided
Height	481 mm
Depth	25 mm

Width	1420 mm
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated rear panel

Accessories

Multimedia swivel arm with multi-function mounting Number of joints 1	928270 1
Multifix suitable for type 300	928201 300
Support column for hooking into perforated panel Height 481 mm	928060 481
Multifix suitable for type 1000	928201 1000
Multifix suitable for type 500	928201 500
Multimedia swivel arm with notebook holder Number of joints 2	928275 2
Multimedia swivel arm with multi-function mounting Number of joints 2	928270 2