

Garant

Slim hydraulic chuck, SK 40 A = 80, Clamping \varnothing D1: 8mm



Order data

Order number	302089 8
GTIN	4062406114824
Item class	31A

Description

Version:

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.** For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon key with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302187.

Technical description

\varnothing D ₃	18.3 mm
Clamping \varnothing D ₁	8 mm
\varnothing D ₂	14 mm
External \varnothing D	49.5 mm
L ₂	40 mm

Overhang dimension A	80 mm
Adapter	SK 40 A = 80
Arbor standard	ISO 7388-1
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

ER collet Nominal clamping Ø d 2,5 mm	308878 2,5
ER collet Nominal clamping Ø d 4 mm	308878 4
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud sealed suitable for steep tapers 40	308660 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud sealed suitable for steep tapers 40	308635 40
Torque wrench with reversible ratchet maximum torque 200 N·m	656050 200
ER collet Nominal clamping Ø d 3,5 mm	308878 3,5
Pull stud sealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 2 mm	308878 2
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
ER collet Nominal clamping Ø d 1 mm	308878 1
	308801 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

Pull stud 60°sealed suitable for steep tapers 40	308785 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
ER collet Nominal clamping Ø d 4,5 mm	308878 4,5
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER chuck key1/2 inch socket for ER collet chuck 40	309700 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
ER chuck key for ER collet chuck 40	309680 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Wrench for ER Mini nuts for ER collet chuck 8	309740 8
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER collet Nominal clamping Ø d 5 mm	308878 5
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
ER collet Nominal clamping Ø d 1,5 mm	308878 1,5
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet Nominal clamping Ø d 3 mm	308878 3