

**Garant****Cermet reaming head HPC H7 steel Blind hole, uncoated, Nominal Ø D: 17mm****Order data**

Order number	239715 17
GTIN	4062406115531
Item class	23A

**Description****Version:**

Interchangeable head reamer system **finish ground for fit IT7**. Cutter geometry matched to the application.

**System concentricity  $\leq 5 \mu\text{m}$  (depending on the head and holder) when mounted.**

With short, straight flutes.

**Application:**

**For blind holes.**

For HPC/HSC reaming.

**Note:**

**Total usable length** =  $L_1$  (arbor No. 239740 / 239745) +  $l$  (interchangeable head No. 239710 to 239720).

Suitable assembly wrench No. 219987. Insert for torque wrench No. 219986.

Further sizes available on request.

**Technical description**

Nominal Ø D	17 mm
Number of cutting edges Z	6
Cutter length $l_1$	8 mm
Feed $f$ in steel $< 1100 \text{ N/mm}^2$	0.6 mm/rev.
Head length $l$	22 mm

Arbor size	12 mm
Width across flats	10 mm
Series	TopCut
Coating	uncoated
Tool material	Cermet
Standard	Manufacturer's standard
Hole tolerance	H7
Application for type of drilling	for blind holes
Machining strategy	HPC
Through-coolant	yes
Semi-Standard	yes
suitable arbor	GARANT TopCut
Type of product	Cutter insert for reaming

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	120 m/min	P
GG	suitable only under restricted conditions	160 m/min	K
G GG	suitable only under restricted conditions	140 m/min	K
Oil	suitable		
wet maximum	suitable		