

## Garant

### Media track for individual configuration, suitable for type: 1500



#### Order data

Order number	928411 1500
GTIN	4062406115876
Item class	91P

#### Description

##### Version:

Of sheet metal **modular design**. All power components include **cables** and **plugs**. The modules and covers can be changed / positioned as desired.

- Cable slots are provided on the upper, lower, and end faces for power supplies and for linking multiple media tracks together.

##### Electrical pre-installation with industrial plug-in system (applies only to media tracks):

1 pc. distribution block No. 928492 with 5-pin feed/supply cable and 5 pcs. 3-pin sockets,  
1 pc. 5-pin plug connector No. 928490 size 5 included for the feed cable.

##### Description:

##### Technical data for industrial plug-in system (No. 928490; 928491; 928492):

- **Maximum connection value 230 V / AC, 16 A or 400 V / AC, 16 A.**
- **Total load capacity at AC: 3.5 kW.**
- **Maximum connected load, three-phase AC: 10.5 kW.**
- **Conductor cross-section of the pre-assembled cables:**
  - 3 × 1.5 mm<sup>2</sup> for single-phase AC (L, N, PE)**
  - 5 × 1.5 mm<sup>2</sup> for three-phase AC (L1, L2, L3, N, PE)**
- **Protection class 1**
- **Index of Protection IP 20.**

##### Colour:

RAL 7035 light grey **powder coated**.

##### Note:

- **Suitable for screwing on to the worktop.**
- **Not suitable for mounting between support columns.**
- **Initial connections and also the connection of plugs or sockets to cables should only be performed by a qualified electrician!**

#### Technical description

Width	1500 mm
Installation height	139 mm
Empty modules (1 unit / 2 units / 3 units)	2× / 1× / 3×
suitable for type	1500
Divider unit	13 units
Depth	100 mm
Nominal voltage	250 V
Plug type, input	GST plug-in system
On/Off switch	no
Type of current	AC
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

---

## Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type 0/2	928470 0/2