

Garant

Diabolo solid carbide HPC drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 13/32



Order data

Order number	122361 13/32
GTIN	4062406116668
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to strong core and special point geometry. **Convex major cutting edges** with **defined honed edge** ensure the drill has high stability and maximum load capacity.

Special multi-nano layer coating for drilling in hardened steels.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122362 / 122372**.

Form **HE**: order with **No. 122361 / 122371 + 129100HE**.

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 39.52 mm

Overall length L: 102 mm

Shank Ø D_s : 12 mm

Feed f in steel < 60 HRC: 0.11 mm/rev.

Technical description

Shank Ø D_s	12 mm
recommended maximum drilling depth L_2	39.52 mm
Overall length L	102 mm
Tolerance nominal Ø	h7

Data sheet

Number of cutting edges Z	2
Inch nominal Ø corresponds to	10.32 mm
Flute length L _c	55 mm
Feed f in steel < 60 HRC	0.11 mm/rev.
Standard	DIN 6537 K
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Drill depth up to	4×D
Type	H
Point angle	140 °
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	red
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	90 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	80 m/min	P
Steel < 900 N/mm ²	suitable	70 m/min	P
Steel < 1100 N/mm ²	suitable	65 m/min	P
Steel < 1400 N/mm ²	suitable	55 m/min	P
Steel < 55 HRC	suitable	28 m/min	H
Steel < 60 HRC	suitable	16 m/min	H
Steel < 65 HRC	suitable	14 m/min	H

Data sheet

Steel < 67 HRC	suitable	10 m/min	H
TOOLOX 33	suitable only under restricted conditions	30 m/min	H
TOOLOX 44	suitable only under restricted conditions	28 m/min	H
HARDOX 500 < 1600 N/mm ²	suitable only under restricted conditions	28 m/min	H
GG(G)	suitable	70 m/min	K
wet maximum	suitable		
dry	suitable		
Services			

Shank grinding Type HE

129100 HE