

Garant**Media track for individual configuration, suitable for type: 1000****Order data**

Order number	928411 1000
GTIN	4062406115869
Item class	91P

Description**Version:**

Of sheet metal **modular design**. All power components include **cables** and **plugs**. The modules and covers can be changed / positioned as desired.

• Cable slots are provided on the upper, lower, and end faces for power supplies and for linking multiple media tracks together.

Electrical pre-installation with industrial plug-in system (applies only to media tracks):

1 pc. distribution block No. 928492 with 5-pin feed/supply cable and 5 pcs. 3-pin sockets,
1 pc. 5-pin plug connector No. 928490 size 5 included for the feed cable.

Description:**Technical data for industrial plug-in system (No. 928490; 928491; 928492):**

- **Maximum connection value 230 V / AC, 16 A or 400 V / AC, 16 A.**
- **Total load capacity at AC: 3.5 kW.**
- **Maximum connected load, three-phase AC: 10.5 kW.**
- **Conductor cross-section of the pre-assembled cables:**
 - 3 × 1.5 mm² for single-phase AC (L, N, PE)**
 - 5 × 1.5 mm² for three-phase AC (L1, L2, L3, N, PE)**
- **Protection class 1**
- **Index of Protection IP 20.**

Colour:

RAL 7035 light grey **powder coated**.

Note:

- **Suitable for screwing on to the worktop.**
- **Not suitable for mounting between support columns.**
- **Initial connections and also the connection of plugs or sockets to cables should only be performed by a qualified electrician!**

Technical description

Empty modules (1 unit / 2 units / 3 units)	1× / 2× / 1×
Installation height	139 mm
Width	1000 mm
Depth	100 mm
Divider unit	8 units
suitable for type	1000
Nominal voltage	250 V
On/Off switch	no
Plug type, input	GST plug-in system
Type of current	AC
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Power module

Accessories

Module for energy and media Module type 0/1	928470 0/1
Module for energy and media Module type 0/2	928470 0/2