

Garant**Extension base with clamping pot, for type: 120****Order data**

| | |
|--------------|---------------|
| Order number | 360154 120 |
| GTIN | 4045197722850 |
| Item class | 310 |

Description**Version:**

With holes for clamping studs No. 360025 18M16. Alternative attachment via stepless adjustable clamps or an M12 bolt in the T-slot. Attachment hole pattern for **GARANT ZeroClamp zero-point clamping system** (pitch 200 mm). Manual operation or air cushion movement across the machine table.

Clamping pot with \varnothing 90 mm or 120 mm for mounting the centring vice No. 360130.

Application:

- **5-face machining on multi-axis machining centres.**
- **As a cost-effective clamping solution for use with the GARANT ZeroClamp zero-point clamping system or with pallet and automated systems, or directly on to the machine table.**

Material:

Steel

Suitable for :

Centring vice No. 360130 in combination with centring/adapter plate No. 360132.

Note:

Size 80/4 – size120/4 – higher support torque for maximum stability.

Length: 320 mm

Width: 120 mm

Height: 125 mm

Clamping studs reference dimension: 200 mm

Clamping pot \varnothing : 138 mm

Number of location holes for clamping studs: 2

Technical description

| | |
|---|------------------|
| Width | 120 mm |
| for type | 120 |
| Height | 125 mm |
| Length | 320 mm |
| Clamping pot \varnothing | 138 mm |
| Clamping studs reference dimension | 200 mm |
| Number of location holes for clamping studs | 2 |
| Type of product | Vice accessories |

Accessories

| | |
|---|--------------|
| ZeroClamp clamping stud with internal thread Type 18M16 | 360025 18M16 |
|---|--------------|