


Garant

Diabolo solid carbide HPC drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 3/16



Order data

Order number	122371 3/16
GTIN	4062406116842
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to strong core and special point geometry. **Convex major cutting edges** with **defined honed edge** ensure the drill has high stability and maximum load capacity.

Special multi-nano layer coating for drilling in hardened steels.

Recommendation:

Maximum drilling depth:

flute length (see table) less $1.5 \times \text{nominal } \varnothing$.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122362 / 122372**.

Form **HE**: order with **No. 122361 / 122371 + 129100HE**.

Standard: DIN 6537 K

Tolerance nominal \varnothing : h7

Number of cutting edges Z: 2

Tolerance nominal \varnothing : h7

recommended maximum drilling depth L_2 : 16.86 mm

Overall length L: 66 mm

Shank $\varnothing D_s$: 6 mm

Feed f in steel < 1100 N/mm^2 : 0.15 mm/rev.

Feed f in steel < 60 HRC: 0.04 mm/rev.

Technical description

Standard	DIN 6537 K
----------	------------

Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	6 mm
Inch nominal \varnothing corresponds to	4.76 mm
Feed f in steel < 60 HRC	0.04 mm/rev.
Flute length L_c	24 mm
Overall length L	66 mm
Feed f in steel < 1100 N/mm ²	0.15 mm/rev.
Number of cutting edges Z	2
recommended maximum drilling depth L_2	16.86 mm
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
	4xD
Type	H
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	red
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	120 m/min	P
Steel < 750 N/mm ²	suitable	100 m/min	P
Steel < 900 N/mm ²	suitable	85 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P

Steel < 1400 N/mm ²	suitable	55 m/min	P
Steel < 55 HRC	suitable	28 m/min	H
Steel < 60 HRC	suitable	16 m/min	H
Steel < 65 HRC	suitable	14 m/min	H
Steel < 67 HRC	suitable	10 m/min	H
TOOLOX 33	suitable	30 m/min	H
TOOLOX 44	suitable	28 m/min	H
HARDOX 500 < 1600 N/mm ²	suitable	28 m/min	H
GG(G)	suitable	70 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		

Services

Shank grinding Type HE

129100 HE