



Solid carbide milling cutter with chip separators TPC, TiAlN, Ø f8 DC: 8mm



Order data

| | |
|--------------|---------------|
| Order number | 203095 8 |
| GTIN | 4062406117344 |
| Item class | 12X |

Description

Version:

High-performance end mill for general-purpose applications, **specially designed for TPC applications.**

Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Offset chip breakers for controlled chip breaking.

Note:

h_{max} : The values stated in the table are maximum values. For finishing operations we recommend items No. 204012, 204014 and 204015.

$a_{e,max} = 0.07 \times D$ for TPC machining.

Technical description

| | |
|---|------------------------|
| Cutting edge Ø D_c | 8 mm |
| Tolerance nominal Ø | f8 |
| Direction of infeed | horizontal and oblique |
| Recess Ø D_1 | 7.8 mm |
| Shank | DIN 6535 HB to h6 |
| Average chip thickness h_{max} for TPC milling in Toolox 44 HRC | 0.042 mm |
| Corner chamfer width at 45° | 0.16 mm |
| Helix angle | 40 degrees |
| Overhang length L_1 incl. recess | 30 mm |

| | |
|--|-------------------------|
| Overall length L | 68 mm |
| Flute length L _c | 24 mm |
| No. of teeth Z | 5 |
| Balance quality with shank | G 2.5 with HB |
| Shank Ø D _s | 8 mm |
| Corner chamfer angle | 45 degrees |
| Number of chip separators | 1 |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | N |
| Helix angle characteristic | unequal spacing |
| Spacing of the cutters | unequal spacing |
| Cutting width a _e for milling operation | 0.07×D |
| Through-coolant | no |
| Machining strategy | TPC |
| Colour ring | green |
| Type of product | End / face mill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------|----------------|----------|
| Steel < 500 N/mm ² | suitable | 380 m/min | P |
| Steel < 750 N/mm ² | suitable | 340 m/min | P |
| Steel < 900 N/mm ² | suitable | 300 m/min | P |
| Steel < 1100 N/mm ² | suitable | 230 m/min | P |
| Steel < 1400 N/mm ² | suitable | 150 m/min | P |
| TOOLOX 33 | suitable | 60 m/min | H |
| TOOLOX 44 | suitable | 40 m/min | H |

| | | | |
|-------------------------------------|---|-----------|---|
| HARDOX 500 < 1600 N/mm ² | suitable | 25 m/min | H |
| INOX < 900 N/mm ² | suitable | 220 m/min | M |
| INOX > 900 N/mm ² | Suitable only under restricted conditions | 150 m/min | M |
| Uni | Suitable | | |
| wet maximum | suitable | | |
| dry | suitable only under restricted conditions | | |
| Air | suitable | | |