

**Garant****Burr, Carbide, Type: T1610/8****Order data**

Order number	541000 T1610/8
GTIN	4062406115791
Item class	51D

**Description****Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Deburring head (internal)** with left-hand helical toothing and 45° angle for **chamfering**.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Note:**

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

**Technical description**

Head Ø	16 mm
Overall length	120 mm
Tooth type abbreviation	Z3

Shank Ø	8 mm
Angle	45 degrees
Toothing grit designation	medium
Shape description	Deburring
Head length	10 mm
Series	#Tooth configuration Z3
Tool material	Carbide
Type of product	Burr