



## Burr Z7 – medium, diamond cut, Carbide, Type: L1630



### Order data

Order number	540750 L1630
GTIN	4045197723734
Item class	52D

### Description

#### Version:

Shank Ø 6 mm.

**HOLEX** burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round cone shape** (KEL).

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Tooth type abbreviation	Z7
Overall length	78 mm
Shape	L1630
Head Ø	16 mm
Shape description	round cone
Type of cut	staggered teeth
Toothing grit designation	medium
Shank Ø	6 mm
Head length	33.3 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		