



Burr Z7 – medium, diamond cut, Carbide, Type: M1225



Order data

Order number	540750 M1225
GTIN	4045197723710
Item class	52D

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Pointed cone shape**(SKM).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	70 mm
Tooth type abbreviation	Z7
Type of cut	staggered teeth
Head Ø	12 mm
Toothing grit designation	medium
Shape description	pointed cone
Shape	M1225
Shank Ø	6 mm
Head length	25 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		