



Burr Z7 – medium, diamond cut, Carbide, Type: F0618



Order data

Order number	540750 F0618
GTIN	4045197723666
Item class	52D

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Head Ø	6 mm
Type of cut	staggered teeth
Tooth type abbreviation	Z7
Toothing grit designation	medium
Overall length	50 mm
Shape	F0618
Shape description	round arch
Shank Ø	6 mm
Head length	18 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		