



Burr Z7 – medium, diamond cut, Carbide, Type: C1625



Order data

Order number	540750 C1625
GTIN	4045197723543
Item class	52D

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Toothing grit designation	medium
Shape	C1625
Overall length	70 mm
Tooth type abbreviation	Z7
Shape description	ball nose
Type of cut	staggered teeth
Head Ø	16 mm
Shank Ø	6 mm
Head length	25 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		