



Burr Z7 – medium, diamond cut, Carbide, Type: AS1225



Order data

| | |
|--------------|---------------|
| Order number | 540750 AS1225 |
| GTIN | 4045197723482 |
| Item class | 52D |

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape (ZYAS), with end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|--------------------------|
| Shape description | Cylindrical with end cut |
| Shape | AS1225 |
| Overall length | 70 mm |
| Head Ø | 12 mm |
| Tooth type abbreviation | Z7 |
| Toothing grit designation | medium |
| Type of cut | staggered teeth |
| Shank Ø | 6 mm |
| Head length | 25 mm |
| Series | #Tooth configuration Z7 |

| | |
|-----------------|---------|
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |