



Burr Z7 – medium, diamond cut, Carbide, Type: A1020



Order data

| | |
|--------------|---------------|
| Order number | 540750 A1020 |
| GTIN | 4045197723383 |
| Item class | 52D |

Description

Version:

Shank Ø 6 mm.

HOLEX burrs are manufactured from highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape (ZYA), without end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|-----------------------------|
| Tooth type abbreviation | Z7 |
| Head Ø | 9.5 mm |
| Toothing grit designation | medium |
| Type of cut | staggered teeth |
| Overall length | 64 mm |
| Shape | A1020 |
| Shape description | Cylindrical without end cut |
| Shank Ø | 6 mm |
| Head length | 19 mm |
| Series | #Tooth configuration Z7 |

| | |
|-----------------|---------|
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |