

Garant
Lever lock toolholder, right-hand, Shank / insert size: 40/19mm

Order data

| | |
|--------------|---------------|
| Order number | 250018 40/19 |
| GTIN | 4062406119218 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| ISO code toolholder | PCLNR/L 4040S19 |
| Series | QuickTurn |
| suitable indexable insert | CN.. 1906.. |
| Functional width L ₄ | 50 mm |
| Lever | 259015 1 |
| Insert size | 19 mm |
| Shim punches pack | 259047 1 |
| Shank size | 40 mm |
| Shim pins pack | 259044 1 |
| Head length L ₁ | 45 mm |
| Overall length L | 250 mm |
| Shim | 259031 17 |
| Lever screw | 259018 1 |
| Standard | DIN ISO 5610 |
| Application type | right-hand |
| Through-coolant | no |

| | |
|------------------------|-------------------------------|
| Setting angle κ | 95 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|----------------------------------|-----------|
| Set of shim pins10 pieces Type 7 | 259044 7 |
| Shim Type 16 | 259031 16 |
| Lever screw Type 1 | 259018 1 |
| Lever screw Type 13 | 259018 13 |
| Shim Type 36 | 259031 36 |
| Lever Type 13 | 259015 13 |
| Lever Type 1 | 259015 1 |
| Shim punches set10 pieces Type 1 | 259047 1 |
| Set of shim pins10 pieces Type 1 | 259044 1 |