

ALLURIS

FMI-B50 Digital precision force gauge (USB), Measuring range: 2500N**Order data**

Order number	478987 2500
GTIN	4260244680895
Item class	47F

Description**Version:**

- **Sturdy force gauges in a handy aluminium die-cast housing for compressive and tensile forces from 0.001 to 2500 N.**
- **Overload protection up to 500% and protected measurement shaft.**
- **Attachment thread for additional handles.**
- **Precise positioning in test stands by a guide pin.**
- **High measurement rate for precise recording of peak values to determine fracture or tearing forces.**
- **Measured value memory with statistical analysis and limit value monitoring.**
- **USB interface for data transmission to a PC.**

Advantage:

Data evaluation and test bench control in combination with motorised test stands. **Supplied with DAkkS calibration certificate.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Measurement of compressive and tensile forces in quality assessment and production. For use as a mobile manual measurement gauge both in outdoor areas and in test stands or jigs. Attachment thread integrated into the housing permit attachment in test stands or mounting of additional handles.

Supplied with:

Force gauge in a protective case. Screw-on accessories for force transfer (flat head, slot head, cone, hook). Quick-start instructions.
Software FMI-AnalyzePro+.

Technical description

Error limit	±0.15 maximum value (±1 digit) %
Connection thread	M10
Length	150 mm
IP Index of Protection	IP 65
Width	82 mm
Measuring range	2500 N
Resolution	1 N
Height	29 mm
Power supply	Mains operated
Interface	USB interface
Measurement technology	digital
Calibration	Price on request
Type of product	Draw bar pulling force gauge