

Garant

Electrically height-adjustable workstation (4 lift columns) Load capacity max. 1000 kg, Type: 1500

**Order data**

Order number	920316 1500
GTIN	4062406119713
Item class	91S

Description**Version:**

Base frame with anodised aluminium lift unit. With cross bracing for stabilisation. 50mm thick worktop made of beech marine ply. Stepless height adjustment from 740 - 1140 mm, quickly and easily selected using the control panel. Control panel with memory function for 3 different working heights.

Supplied with:

4 floor levelling screws.

Colour:

Base frame with aluminium lift unit and steel hollow section RAL 7016 anthracite **powder-coated**.

Recommendation:

Ergonomic working for seated and standing tasks!

Note:

Only cabinet bodies up to maximum 500 mm height can be installed under the worktop.

Height adjustment: 25 mm

Height adjustment range (worktop surface) from – to: 740 - 1140 mm

Width: 1500 mm

Depth: 700 mm

Worktop length: 1500 mm

Worktop depth: 700 mm

Worktop thickness: 50 mm

Technical description

Weight	86 kg
Principle of height adjustment	complete structure
Material of worktop	Beech marine ply
Worktop length	1500 mm
Stepless height adjustment	yes
Width	1500 mm
Worktop depth	700 mm
Height adjustment range (worktop surface) from – to	740 - 1140 mm
Depth	700 mm
Worktop thickness	50 mm
Continuous load capacity	750 kg
Surface worktop	clear varnished
Control panel with display and memory functions	yes
maximum load capacity	1000 kg
Plug type, input	F
Nominal voltage	250 V
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Type of height adjustment	electrical
Insert thickness	50 mm
Height adjustment	25 mm
Type of product	Work table