

Garant GRIDLINE

eLevel workstation with dark grey Eluplan worktop, Length: 2000mm



Order data

| | |
|--------------|---------------|
| Order number | 920012 2000 |
| GTIN | 4062406119478 |
| Item class | 91P |

Description

Version:

Workstation eLevel height steplessly adjustable electrically. Height adjustment by an electronic control panel. Control panel with display and memory functions. Push-button adjustment for a suitable **height of the entire workstation**.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift columns anodised aluminium, **not configurable**.

Side panel and rear panel RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

Technical description

| | |
|------------------|--|
| Surface worktop | Coating anti-static, highly abrasion-resistant, medium hardness, not colour-fast |
| Worktop covering | Eluplan (plastic), (linoleum covering) |

| | |
|---|--|
| Coating thickness | 2 mm |
| Principle of height adjustment | complete structure |
| Weight | 93 kg |
| Stepless height adjustment | yes |
| Height adjustment range (worktop surface) from – to | 700 - 1000 mm |
| Depth | 800 mm |
| Series | Workstation |
| Model | eLevel |
| Control panel with display and memory functions | yes |
| Worktop length | 2000 mm |
| Material of worktop | Eluplan |
| Worktop depth | 700 mm |
| Width | 2000 mm |
| Colour of worktop surface | dark grey |
| Worktop thickness | 40 mm |
| Plug type, input | F |
| Nominal voltage | 250 V |
| Height adjustment workstation | 700-1000 mm |
| Design version | Steel hollow section construction |
| Workbench/desk load capacity - maximum distributed load (on wood) | 250 kg |
| Type of height adjustment | electrical |
| Insert thickness | 40 mm |
| Height adjustment | 25 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Work table |

Accessories

| | |
|--|--------------|
| Drawer casing 24G with drawers Height / number of drawers 500/5 | 927600 500/5 |
| Drawer casing 16G with drawers Height / number of drawers 300/2 | 927300 300/2 |
| Support columns Height 200 mm | 928010 200 |
| Drawer casing 24G with drawers Height / number of drawers 400/4 | 927600 400/4 |
| Drawer casing 16G with drawers Height / number of drawers 300/3 | 927300 300/3 |
| 16G computer casing Height 500 mm | 927335 500 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/3 | 927315 500/3 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 400/4 | 927315 400/4 |
| Support columns Height 1362 mm | 928010 1362 |
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/5 | 927315 500/5 |
| Drawer casing 16G with drawers Height / number of drawers 400/3 | 927300 400/3 |
| PC holder Type M | 928753 M |
| Drawer casing, 24G mobile Casing height / number of drawers 500/5 mm | 927620 500/5 |
| Drawer casing 16G with drawers Height / number of drawers 400/4 | 927300 400/4 |
| Side plate for workstations Suitable for workstation depth 800 mm | 920350 800 |
| Drawer casing 24G with drawers Height / number of drawers 300/2 | 927600 300/2 |
| Drawer casing 24G with drawers Height / number of drawers 200/1 | 927600 200/1 |
| Multifix suitable for type 300 | 928201 300 |
| Keyboard drawer Type 1 | 927341 1 |
| Support columns Height 962 mm | 928010 962 |

| | |
|--|--------------|
| Drawer casing, 16G mobile Casing height mm / number of drawers 500/4 | 927315 500/4 |
| Support columns Height 481 mm | 928010 481 |
| Drawer casing 24G with drawers Height / number of drawers 300/3 | 927600 300/3 |