



Straight die grinder, Type: 722320



Order data

Order number	077261 722320
GTIN	4014586879451
Item class	03F

Description

Version:

- Exceptionally handy straight die grinder.
- Quiet running due to multiple spindle bearings.
- Powerful motor with high cutting power.
- Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.
- Suitable for grinding points and carbide milling cutters.
- Robust straight grinder, runs at reduced speed.
- Also suitable for working on stainless steel.
- POWERtronik with speed stabilisation and overload protection.

Supplied with:

Collet Ø 6 mm, 2 chuck wrenches 13 AF and 17 AF.

Note:

Straight die grinders are approved for use with burrs up to a Ø of 12 mm.

Technical description

maximum vibration to EN	< 2.5 m/s ²
electronic speed pre-selection	yes
Manufacturer's designation	GSZ8-90PEL
Cable length	4 m

Weight	1.8 kg
Power consumption	710 W
Speed range	2500 - 9000 min ⁻¹
maximum collet Ø	6 mm
Power supply	Mains operated
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	077268 6
---	----------