

Garant

GARANT Master Titan solid carbide milling cutter with more chip separators TPC, TiAlN, Ø e8 DC: 4mm



Order data

Order number	203122 4
GTIN	4062406120030
Item class	11Z

Description

Version:

High-performance milling cutter specially designed for general-purpose TPC applications. Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Application:

Especially for milling **titanium and titanium alloys**.

Note:

h_{max} : The values stated in the table are maximum values.

$a_{e,max}$: = $0.08 \times D$ for TPC machining.

Technical description

Overall length L	57 mm
Shank	DIN 1835 B to h5
No. of teeth Z	6
Direction of infeed	horizontal and oblique
Recess Ø D ₁	3.9 mm
Balance quality with shank	G 2.5 with HB
Helix angle	40 degrees
Tolerance nominal Ø	e8

Average chip thickness h_{\max} for TPC milling in titanium > 850 N/mm ²	0.03 mm
Shank $\varnothing D_s$	6 mm
Flute length L_c	11 mm
Cutting edge $\varnothing D_c$	4 mm
Corner rounding r_v	0.1 mm
Series	Master Titan
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0,08×D
Through-coolant	no
Machining strategy	TPC
Colour ring	pink
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Ti > 850 N/mm ²	suitable	120 m/min	S
wet maximum	suitable		