



Linishing machine GHB15-50, Type: 79030100



Order data

Order number	077780 79030100
GTIN	4014586884516
Item class	03F

Description

Version:

1500 Watt motor, adjustable handles, external motor position can be turned, no tools required to change the belt, round recess for linishing pipes and profiles. Hand-held linishers for flexible use on site.

Supplied with:

Linishing machine, 1 linishing belt 36 grit.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Suitable belts can be found under No. 558444. Further belts available on request.

Manufacturer's designation: GHB 15-50

Power consumption: 1500 W

maximum speed: 8500 rpm

Tape width: 50 mm

Band length: 1000 mm

Weight: 5.6 kg

Technical description

Manufacturer's designation	GHB 15-50
maximum vibration to EN	< 2.5 m/s ²
Band length	1000 mm
Power consumption	1500 W
Tape width	50 mm
Weight	5.6 kg
maximum speed	8500 rpm
Power supply	Mains operated
Type of product	Linishing machine

Accessories

Linishing belt Cubitron™II 947A Grit 120	558444 120
Linishing belt Cubitron™II 947A Grit 40	558444 40
Linishing belt Cubitron™II 947A Grit 60	558444 60
Linishing belt Cubitron™II 947A Grit 80	558444 80
Linishing station GHBD Type 99001012	077782 99001012