


**Garant****Perforated back panels, suitable for worktop length: 1500mm****Order data**

Order number	920365 1500
GTIN	4062406120801
Item class	91S

**Description****Version:**

Made of folded sheet metal with □ 9×9 mm holes at 37 mm pitch.  
For attachment to the back of workstations with electric height adjustment, for light loads.  
Perforated panels are bolted to the rear cross braces from within.

**Suitable for:**

Workstations with electric height adjustment, for light loads No. 920301 – 920306.

**Supplied with:**

Fastening material.

**Colour:**

Anthracite RAL 7016 **powder-coated.**

**Technical description**

Width	1245 mm
Depth	70 mm
Weight	7.4 kg
Height	334 mm
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Type of product

Rear panel