

KÄRCHER**Industrial vacuum cleaner, Manufacturer's designation: IVR-L65****Order data**

Order number	078522 IVR-L65
GTIN	4054278029696
Item class	07D

Description**Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

1-motor 1.2 kW industrial vacuum cleaner with **tilting mobility trolley** and **65 litre tank**.

Supplied with:

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

Power consumption: 1200 W

Container volume: 65 l

Connection width: DN50 mm

Length: 742 mm

Width: 500 mm

Height: 1100 mm

Technical description

Vacuum	230 mbar
Length	742 mm
Operating noise	71 dB(A)
Container volume	65 l
Connection width	DN50 mm
Width	500 mm
Cable length	6 m
Number of turbines	1
Air flow volume	59 l/s
Height	1100 mm
Weight	43 kg
Power consumption	1200 W
Dust class – vacuum cleaner	L
Manufacturer's designation	IVR-L 65/12-1 Tc
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Swarf basket for the industrial vacuum cleaner Volume 20 l	078524 20
Set for vacuuming chips and liquids Connection width DN40	078529 DN40
Reducing adaptor Connection width DN40	078533 DN40
Set for vacuuming chips and liquids Connection width DN42	078529 DN42