

Garant

Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC m6 (mm or inch): 7/32



Order data

Order number	123214 7/32
GTIN	4062406121198
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

For process reliability when using the 12×D drill, an initial centre drilling with No. 121068 – 121130 is necessary.

Standard: Manufacturer's standard

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 69.66 mm

Tolerance nominal Ø: m6

Overall length L: 116 mm

Shank Ø D_s : 6 mm

Feed f in stainless steel > 900 N/mm²: 0.12 mm/rev.

Technical description

Standard	Manufacturer's standard
Tolerance nominal Ø	m6
recommended maximum drilling depth L_2	69.66 mm
Inch nominal Ø corresponds to	5.56 mm

Overall length L	116 mm
Feed f in stainless steel > 900 N/mm ²	0.12 mm/rev.
Shank Ø D _s	6 mm
Flute length L _c	78 mm
Number of cutting edges Z	2
Coating	TiAlN
Tool material	Solid carbide
Version	12xD
Point angle	135 °
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	90 m/min	P
Steel < 750 N/mm ²	suitable	75 m/min	P
Steel < 900 N/mm ²	suitable	70 m/min	P
Steel < 1100 N/mm ²	suitable	55 m/min	P
Steel < 1400 N/mm ²	suitable	32 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M
INOX > 900 N/mm ²	suitable	60 m/min	M
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

