

**Garant****Mini burr Z FINE – very fine, Carbide, Type: M0311****Order data**

Order number	546840 M0311
GTIN	4045197726452
Item class	51D

**Description****Version:**

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Head $\varnothing$	3 mm
Toothing grit designation	very fine
Shape	M0311
Shape description	pointed cone

Overall length	40 mm
Tooth type abbreviation	Z FINE
Shank Ø	3 mm
Head length	11 mm
Series	Tooth configuration Z FINE
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		