



## HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7 (mm or inch): 6,15



### Order data

Order number	122502 6,15
GTIN	4062406121723
Item class	12F

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Standard: DIN 6537 K

Tolerance nominal  $\varnothing$ : h7

Number of cutting edges Z: 2

Tolerance nominal  $\varnothing$ : h7

recommended maximum drilling depth  $L_2$ : 24.775 mm

Overall length L: 79 mm

Shank  $\varnothing D_s$ : 8 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.18 mm/rev.

### Technical description

recommended maximum drilling depth $L_2$	24.775 mm
Overall length L	79 mm
Tolerance nominal $\varnothing$	h7
Shank $\varnothing D_s$	8 mm
Flute length $L_c$	34 mm
Nominal $\varnothing D_c$	6.15 mm

Number of cutting edges Z	2
Standard	DIN 6537 K
Feed f in steel < 900 N/mm <sup>2</sup>	0.18 mm/rev.
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
wet maximum	suitable		
dry	suitable		

