

Garant**Precision bore gauge, Measuring range: 50-150mm****Order data**

Order number	435190 50-150
GTIN	4045197726391
Item class	41C

Description**Version:**

Precision two-point dial bore gauge with spring-loaded centring disc. **Lightweight**, stable version with **CRP elements**, hence reduced **thermal expansion** and increased **corrosion protection**. Hand heat insulation on the frame additionally reduces the effects of temperature. Smooth and precise transmission of the contact point travel by a curved segment. Fixed contact point with hardened steel ball allows adjustment to different \varnothing .

Version of the advertising text:

- **Lightweight, stable version with CRP elements.**
- **Less thermal expansion.**
- **Increased protection against corrosion.**

Application:

For precise measuring of bores in terms of \varnothing , roundness, and cylindricity as well as measurements of internal profiles.

Supplied with:

Precision bore gauge complete in a wooden case (without dial indicator).

Optional extras:

Precision dial comparator No. 434674, inductive precision dial comparator No. 434670, dial indicator with anticlockwise scale 434807 size 10, digital dial indicator 434322, setting rings No. 484030.

Note:

When using precision dial indicators, an additional extension No. 434920 size 10 or contact point No. 434900 size 16 is required.

Technical description

Repetition accuracy without dial gauge	1 µm
Measurement depth	178 mm
Number of contact points	11
Measuring range	50 - 150 mm
Number of measuring discs	3
Centring plate width	42.3 mm
Standard	Manufacturer's standard
Packaging	sturdy box
Calibration	C4
Type of product	2-point precision bore gauge

Services

Calibration Precision bore gauge (types B + C) maximum measuring range 160 mm	023210 160
---	------------

Accessories

Adapter for two-point bore gauges 1 piece Type 35-90	439914 35-90
Extension for contact points Length L 10 mm	434920 10
Steel contact point Type 16	434900 16
Precision dial indicator shock-resistant Measuring range / Body Ø 1/58 mm	433090 1/58
Dial indicator shock-resistant Measuring range / Body Ø 10/58 mm	432110 10/58