

## Garant

### GARANT Master Alu SlotMachine solid carbide roughing end mill HPC, DLC, Ø e8 DC: 5mm



#### Order data

Order number	205250 5
GTIN	4062406122201
Item class	11X

#### Description

##### Version:

For roughing.

Special profile for machining non-ferrous metals.

##### Advantage:

**Optimised flute form, eccentric relief ground, generous chip spaces.**

Up to  $2 \times D$  into solid material at very high feed rates and smooth cutting action.

Ramping capability up to  $45^\circ$ .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

#### Technical description

Overall length L	57 mm
Direction of infeed	horizontal, oblique and vertical
Helix angle	35 degrees
Shank Ø D <sub>s</sub>	6 mm
Feed f <sub>z</sub> for slot milling in short-chipping aluminium	0.06 mm
Tolerance nominal Ø	e8
Feed f <sub>z</sub> for side milling in short-chipping aluminium	0.08 mm
Shank	DIN 6535 HA to h6
No. of teeth Z	3

Cutting edge $\varnothing D_c$	5 mm
Balance quality with shank	G 2.5 with HA
Flute length $L_c$	9 mm
Corner rounding $r_v$	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.4×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N
PA 66	suitable only under restricted conditions	120 m/min	N
PEEK	suitable only under restricted conditions	100 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable
<b>Services</b>	
Shank grinding Type HB	129100 HB