

Garant

GARANT Master Alu PickPocket solid carbide roughing end mill HPC, DLC, Ø e8 DC: 14mm



Order data

| | |
|--------------|---------------|
| Order number | 202004 14 |
| GTIN | 4062406126018 |
| Item class | 11X |

Description

Version:

With the latest generation of DLC coating sp².

For roughing and finishing.

Up to 2 × D into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to 45°.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Technical description

| | |
|--|----------------------------------|
| No. of teeth Z | 3 |
| Shank Ø D _s | 14 mm |
| Feed f _z for side milling in short-chipping aluminium | 0.17 mm |
| Direction of infeed | horizontal, oblique and vertical |
| Tolerance nominal Ø | e8 |
| Overall length L | 83 mm |
| Balance quality with shank | G 2.5 with HA |
| Shank | DIN 6535 HA to h6 |
| Flute length L _c | 26 mm |

| | |
|---|--------------------------------------|
| Recess $\varnothing D_1$ | 13.8 mm |
| Overhang length L_1 incl. recess | 36 mm |
| Cutting edge $\varnothing D_c$ | 14 mm |
| Helix angle | 42 degrees |
| Feed f_z for slot milling in short-chipping aluminium | 0.12 mm |
| Corner rounding r_v | 0.32 mm |
| Series | Master Alu |
| Coating | DLC |
| Tool material | Solid carbide |
| Standard | DIN 6527 |
| Type | W |
| Helix angle characteristic | unequal spacing |
| Spacing of the cutters | unequal spacing |
| Cutting width a_e for milling operation | Full slot cutting depth $1 \times D$ |
| Cutting width a_e for milling operation | Full slot cutting depth $1 \times D$ |
| Through-coolant | no |
| Machining strategy | HPC |
| Colour ring | yellow |
| Type of product | End / face mill |

User data

| | Suitability | V_c | ISO code |
|----------------------------|-------------|-----------|----------|
| Aluminium | Suitable | 550 m/min | N |
| Aluminium (short chipping) | suitable | 500 m/min | N |
| Alu > 10% Si | suitable | 450 m/min | N |
| PMMA acrylic | Suitable | 200 m/min | N |
| PE-HD | Suitable | 160 m/min | N |
| PA 66 | Suitable | 200 m/min | N |

| | | | |
|--------------------|---|-----------|---|
| PEEK | Suitable | 150 m/min | N |
| PF 31 | Suitable | 130 m/min | N |
| PVDF GF20 | Suitable | 180 m/min | N |
| POM GF25 | Suitable | 160 m/min | N |
| PA 66 GF30 | Suitable | 150 m/min | N |
| PEEK GF30 | Suitable | 130 m/min | N |
| PTFE CF25 | Suitable | 160 m/min | N |
| Honeycomb sandwich | suitable only under restricted conditions | 300 m/min | N |
| Cu | Suitable | 160 m/min | N |
| CuZn | Suitable | 200 m/min | N |
| wet maximum | suitable | | |
| wet minimum | suitable only under restricted conditions | | |
| dry | suitable only under restricted conditions | | |
| Air | suitable | | |

Services

Shank grinding Type HB

129100 HB