

Garant

High-precision countersink set with 3 drive flats, long, No. 150376 in a case 90°, TiAlN, Number of countersinks: 6

**Order data**

Order number	150369 6
GTIN	4062406127435
Item class	11M

Description**Version:**

Handy for assembly and workshop use.

High-precision countersink No. 150376, **with long shank with 3 drive flats.**

Application:

High-precision countersinks for chatter-free production of **precise, round 90° countersunk surfaces.**

Content:

1× each countersink: Size 6.3; 8.3; 10.4; 12.4; 16.5; 20.5

Supplied with:

6-piece countersink set in a case.

Technical description

Number of cutting edges Z	3
Number of countersinks	6
Coating	TiAlN

Countersink tip angle	90 degrees
Tool material	HSS
Spacing of the countersink cutting edges	unequal spacing
Standard	Manufacturer's standard
Shank	Shank with h9 and three drive flats
Colour ring	green
Type of product	Stepped drill and countersink

Accessories

High-precision countersink, long, with 3 drive flats90° External Ø Dc 16,5 mm	150376 16,5
High-precision countersink, long, with 3 drive flats90° External Ø Dc 6,3 mm	150376 6,3
High-precision countersink, long, with 3 drive flats90° External Ø Dc 20,5 mm	150376 20,5
High-precision countersink, long, with 3 drive flats90° External Ø Dc 10,4 mm	150376 10,4
High-precision countersink, long, with 3 drive flats90° External Ø Dc 12,4 mm	150376 12,4
High-precision countersink, long, with 3 drive flats90° External Ø Dc 8,3 mm	150376 8,3