

Garant**Rigid foam holder, Type: 1****Order data**

Order number	956820 1
GTIN	4062406127596
Item class	91F

Description**Version:**

Rigid foam holder of sheet metal to take rigid foam inlays of 20G / 500 mm width. With facility for an additional central restraint to secure two foam inlays. Each holder can take 2 rigid foam inlays of size 8×20G or 4 foam inlays of size 8×10G.

Suitable for:

For hanging up in perforated panels □ 9×9 mm in 37 mm grid.
Can also be attached to the worktop with 4 wood screws (not included).

Colour:

Rigid foam holder RAL 7035 light grey, additional holder RAL 7016 anthracite, **powder-coated**.

Note:

Suitable only for foam inlays in which the tools lie virtually flush.
Only limited suitability for the foam inlays listed in the catalogue. Tools must be planned for a close fit in an individually configured foam inlay.

Technical description

Height	440 mm
Depth	110 mm

Usable width	500 mm
Usable height	400 mm
suitable for foam thickness	30 mm
Type	1
Width	500 mm
Type of product	Rigid foam holder