



LED rechargeable work lamp, Type: UNIFORM



Order data

Order number	081516 UNIFORM
GTIN	5708997354070
Item class	08C

Description

Version:

LED rechargeable work lamp with high-power LEDs for high light output. With fold-out swivel support hook and powerful attachment magnet. New generation of the version **UNIFORM**.

Extremely sturdy, with intelligent battery charge display and additional spotlight. Belt clip. High-performance **COB LED technology for extremely bright homogeneous lighting of an area at two levels of brightness.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with charging station and USB charging cable.

Technical description

Illumination	500 lm
Battery voltage	3.7 V
Bulb	LED module
Number of rechargeable batteries contained	1

Power supply	Rechargeable battery powered
Type of rechargeable battery	Lithium-ion
Illumination step 2	250 lm
Battery capacity	3 Ah
Overall length	190 mm
Overall width	60 mm
IP Index of Protection	IP 65
Illumination time	3 h
Illumination time stage 2	6 h
Weight	265 g
ATEX zone	no
Manufacturer's designation	UNIFORM
Type of product	Work lamp

Accessories

USB charger Type CABLE	081512 CABLE
------------------------	--------------