

**Garant**
**SlimLine revolving lathe centre 60°/30°, Morse taper: 4**

**Order data**

Order number	320643 4
GTIN	4062406127282
Item class	31Z

**Description**
**Version:**

- **Precision version with additional stiffness in the bearings.**
- **Precision roller bearings for high concentricity.**
- **Maintenance-free due to lifetime lubrication.**
- **Special seal prevents ingress of dirt and coolant.**
- **MT shank hardened and ground.**
- **With extended centre, point angle 60° / 30°.**
- **With push-off thread and push-off nut.**
- **outstandingly suitable for cutting threads and splining.**

**Description:**

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

**Advantage:**

**Push-off nut can be removed forwards** thus eliminating any obstruction to the machining process.

**Application:**

Machining small and very small parts such as thread machining with optimum access to the flat face.

**Supplied with:**

Including draw-off nut.

Body Ø D: 38 mm

Overall length L: 185 mm

Reach B: 82 mm

largest centre point Ø 60° A: 10 mm

largest centre point  $\varnothing$  30° A: 20 mm  
maximum radial run-out: 0.005 mm

## Technical description

Body $\varnothing$ D	38 mm
largest centre point $\varnothing$ 30° A	20 mm
largest centre point $\varnothing$ 60° A	10 mm
maximum radial run-out	0.005 mm
for workpiece weight	1400 kg
Overall length L	185 mm
Morse taper	MT4
maximum speed	4000 min <sup>-1</sup>
Reach B	82 mm
Centre point length C	33 mm
Version	With draw-off nut
Type of product	Centring drill