

Garant
Through hole machine tap, uncoated, MF: M30X2,5

Order data

Order number	130000 M30X2,5
GTIN	4062406130565
Item class	10N

Description
Note:

Delivery time: 28 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Technical description

Overall length L	180 mm
Thread pitch	2.5 mm
Thread \varnothing	30 mm
Shank $\varnothing D_s$	22 mm
Shank square \square	18 mm
Number of clamping slots	4
Tool material	HSS E
Number of cutting edges Z	4
Thread type	M
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX
Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX

Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Tapping hole Ø	27.5 mm
Thread depth	90 mm
Standard	DIN 376
Thread size	M30×2.5
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap