

**Garant****Toolholder for imperial profile broaching tools  $\varnothing d = 8$  mm, Shank  $\varnothing DS: 5/8$ in**

## Order data

Order number	293070 5/8
GTIN	4062406128975
Item class	29K

## Description

**Suitable for:**

CNC and conventional machines.

**Optional extras:**

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

**Note:**

- **Caution: Always use appropriate slotting tool  $\varnothing$ .**
- **Other shank connections on request.**

## Technical description

L	38 mm
Shank length $L_s$	35 mm
Shank type	Plain shank
$\varnothing D$	33 mm
$\varnothing d$	8 mm

Shank size	5/8 in
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

---

## Accessories

Pin spanner for holder Ø 8 mm	293006 8
Pin spanner for holder Ø 5 mm	293006 5
Pin spanner for holder Ø 12 mm	293006 12
Pin spanner for holder Ø 16 mm	293006 16