

Garant**Toolholder for imperial profile broaching tools $\varnothing d = 16$ mm, Shank $\varnothing DS$: 3/4in****Order data**

Order number	293076 3/4
GTIN	4062406129033
Item class	29K

Description**Suitable for:**

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

Shank length L_s	50 mm
L	76 mm
Shank type	Plain shank
$\varnothing d$	16 mm

Ø D	58 mm
Shank size	3/4 in
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

Accessories

Pin spanner for holder Ø 16 mm	293006 16
Pin spanner for holder Ø 12 mm	293006 12
Pin spanner for holder Ø 8 mm	293006 8
Pin spanner for holder Ø 5 mm	293006 5