

**Garant**
**Solid carbide forward / reverse corner rounding cutter, TiAlN, Radius r: 0,4mm**

**Order data**

Order number	208172 0,4
GTIN	4062406131265
Item class	11X

**Description**
**Version:**
**Extra long shank.**

Double ground head **with quadrant profile.**

**Tolerance:** Size = **Radius r  $\pm 0.05$  mm.**

**Application:**

For **universal application** in virtually all materials. The newly developed coating **effectively prevents formation of built-up edges** – even in aluminium and stainless steel.

For **front** and **back deburring** of edges with contours.

**Technical description**

Radius r	0.4 mm
Shank $\varnothing D_s$	8 mm
$L_2 +0.5$	2 mm
small $\varnothing D_3$	7.2 mm
large $\varnothing D_2$	8 mm
Flute length $L_c$	0.4 mm
No. of teeth Z	5
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.01 mm
Overall length L	100 mm
$\varnothing D_1 +0.05$	6 mm
$L_4 +0.5$	26 mm

Radius milling	backwards and forwards
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance of radius contour	± 0.05
Cutting width $a_e$ for milling operation	0.5 $\times$ r for side milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Shank tolerance	h6
Colour ring	green
Type of product	End mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable	125 m/min	N
Alu > 10% Si	suitable	75 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	45 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	40 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	M
GG(G)	suitable	45 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable
Air	suitable
<b>Services</b>	

Shank grinding Type HB	129100 HB
------------------------	-----------